


## Rigid Conduit/IMC Fittings


### Conduit Nipples — Iron/Zinc Plated



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |        | STD. CTN. |
|----------|--------------------|------------------|--------|-----------|
|          |                    | A                | B      |           |
| 841-TB   | 3/8                | 9/16             | 11/16  | 500       |
| HA-401   | 1/2                | 39/64            | 15/16  | 500       |
| HA-402   | 3/4                | 43/64            | 13/16  | 200       |
| HA-403   | 1                  | 7/8              | 17/16  | 100       |
| HA-404   | 1 1/4              | 1 1/8            | 1 3/4  | 100       |
| HA-405   | 1 1/2              | 1 1/8            | 2 1/16 | 50        |
| HA-406   | 2                  | 1 7/16           | 2 9/16 | 50        |
| HA-407   | 2 1/2              | 1 3/4            | 3      | 20        |
| HA-408   | 3                  | 1 1/2            | 3 3/8  | 10        |
| HA-409   | 3 1/2              | 1 3/4            | 4 3/8  | 5         |
| HA-410   | 4                  | —                | —      | 5         |

UL File No. E16592.


### Conduit Nipples Die-Cast Zinc — 1" Long



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |       | STD. CTN. |
|----------|--------------------|------------------|-------|-----------|
|          |                    | A                | B     |           |
| HA-211   | 1/2                | 1                | 15/16 | 1,000     |
| HA-212   | 3/4                | 1                | 13/16 | 500       |
| HA-213   | 1                  | 1                | 17/16 | 250       |

UL File No. E-23018 1/2" & 3/4" only.


### Conduit Nipples Die-Cast Zinc — Insulated



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |      | STD. CTN. |
|----------|--------------------|------------------|------|-----------|
|          |                    | A                | B    |           |
| HA-801   | 1/2                | .98              | .59  | 1,000     |
| HA-802   | 3/4                | 1.18             | .70  | 500       |
| HA-803   | 1                  | 1.50             | .80  | 250       |
| HA-804   | 1 1/4              | 1.75             | 1.06 | 250       |
| HA-805   | 1 1/2              | 2.11             | 1.01 | 100       |
| HA-806   | 2                  | 2.61             | 1.20 | 40        |
| HA-807   | 2 1/2              | 3.13             | 1.49 | 25        |
| HA-808   | 3                  | 3.90             | 1.65 | 10        |
| HA-809   | 3 1/2              | 4.20             | 1.68 | 10        |
| HA-810   | 4                  | 4.79             | 1.73 | 10        |


UL File No. E-23018 1/2" & 3/4" only.

### Conduit Nipples Iron/Zinc Plated — Insulated



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |         | STD. CTN. |
|----------|--------------------|------------------|---------|-----------|
|          |                    | A                | B       |           |
| HA-901   | 1/2                | 43/64            | 1 13/16 | 500       |
| HA-902   | 3/4                | 19/16            | 1 7/32  | 200       |
| HA-903   | 1                  | 7/8              | 1 7/16  | 100       |
| HA-904   | 1 1/4              | 1 1/8            | 1 3/4   | 100       |
| HA-905   | 1 1/2              | 1 1/8            | 2 1/16  | 50        |
| HA-906   | 2                  | 1 7/16           | 2 9/16  | 50        |

### Offset Nipples — Die-Cast Zinc




| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |      | STD. CTN. |
|----------|--------------------|------------------|------|-----------|
|          |                    | A                | B    |           |
| HO-221   | 1/2                | 2.60             | 1.00 | 100       |
| HO-222   | 3/4                | 2.62             | 1.32 | 100       |
| HO-223   | 1                  | 2.68             | 1.51 | 100       |
| HO-224   | 1 1/4              | 2.85             | 1.85 | 50        |
| HO-225   | 1 1/2              | 2.88             | 2.08 | 50        |
| HO-226   | 2                  | 3.19             | 2.71 | 20        |

3/4" offset.

UL File No. E-23018.

### Conduit Nipples Die-Cast Zinc — Non-Insulated



| CAT. NO. | CONDUIT SIZE (IN.) | DIMENSIONS (IN.) |      | STD. CTN. |
|----------|--------------------|------------------|------|-----------|
|          |                    | A                | B    |           |
| HA-201   | 1/2                | .98              | .59  | 1,000     |
| HA-202   | 3/4                | 1.18             | .70  | 500       |
| HA-203   | 1                  | 1.50             | .80  | 250       |
| HA-204   | 1 1/4              | 1.75             | 1.06 | 250       |
| HA-205   | 1 1/2              | 2.11             | 1.01 | 100       |
| HA-206   | 2                  | 2.61             | 1.20 | 40        |
| HA-207   | 2 1/2              | 3.13             | 1.49 | 40        |
| HA-208   | 3                  | 3.90             | 1.65 | 40        |
| HA-209   | 3 1/2              | 4.20             | 1.68 | 40        |
| HA-210   | 4                  | 4.79             | 1.73 | 20        |

UL File No. E-23018 1/2"-2".