



Actual

**Catalog Number:** 035-72775-12  
**Product ID:** 7TBD012980R0004  
**UPC Number:** 78621063120  
**Status:** A

3/4 Inch Insulated Watertight Strain Relief Connector, Straight, Cable Size 0.625 to 0.750 Inch, Steel, Zinc Plated

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Strain Relief Cord Connectors-Straight
Application	Provide Means for Passing a Cord Cable, Armored or Unarmored, Into an Enclosure, Through a Bulk-head or Into a Rigid Conduit
Size	0.625 to 0.750 Inch
Material	Steel

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	None
Material housing	Steel
Surface protection	Zinc coated

#### Packaging

Inner Quantity	10
Outer Quantity	50
Weight Uom	1 lbs. per 100