



Actual

Catalog Number: 035-72775-27
Product ID: 7TBD012360R0008
UPC Number: 78621086883
EAN Number: 05415022435276
Status: A

Zinc Strain Relief Fitting Connector, 5 Pieces

North American Specifications (UNSPSC)

| | |
|------------------|------------------------------------------------------------------------------------------------------------------------------|
| UNSPSC | 39121420 Liquid tight connectors |
| IGCC | 4585 Liquid tight connectors |
| Type | Strain Relief Cord Connectors-Straight |
| Special Features | Throat Inner Diameter is Nylon Coated for Ease of Wire Pull |
| Application | Provide Means for Passing a Cord Cable, Armored or Unarmored, Into an Enclosure, Through a Bulk-head or Into a Rigid Conduit |
| Material | Zinc |

European Specifications (ETIM)

| | |
|---------------------------------------------|--------------------------------------------------------|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch | 1 1/2 inch |
| Model | Straight |
| Revolving thread | N |
| Construction type | External thread |
| Connection type screw connection to housing | Thread |
| Thread type | NPT |
| Thread connection size | None |
| Material housing | Steel |
| Surface protection | Zinc coated |

Packaging

| | |
|---------------------------|-----------------|
| Inner Quantity | 5 |
| Inner Dimensions (inches) | 6x4.5x3 |
| Outer Quantity | 10 |
| Weight Uom | 70 lbs. per 100 |