



Actual

Catalog Number: 035-72775-28
Product ID: 7TBD012370R0017
UPC Number: 78621085632
Status: A

1-1/2 Inch Insulated Watertight Strain Relief Connector, Straight, Cable Size 1.375 to 1.625 Inch, Steel, Zinc Plated

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Strain Relief Cord Connectors-Straight
Application	Provide Means for Passing a Cord Cable, Armored or Unarmored, Into an Enclosure, Through a Bulk-head or Into a Rigid Conduit
Size	1.375 to 1.625 Inch
Material	Steel
Finish	Zinc Plated

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	None
Material housing	Steel
Surface protection	Zinc coated

Packaging

Outer Quantity	5
Outer Dimensions (inches)	7.62x6.6x3.5
Weight Uom	10 lbs. per 100