



Actual

Catalog Number: 10-405
Product ID: 7TAA008610R0001
UPC Number: 78378600474
EAN Number: 05415022189605
Status: A

High temperature Porcelain Wire Connector HI-5. Wire Range #18 to #16 AWG. Stranded Copper. White. 100 pieces

- Three sizes accommodate #18-14AWG stranded Copper
- 300 Volt rated.
- For high temperature applications over 105 degree C

North American Specifications (UNSPSC)

UNSPSC	39121445 Twist on wire connector
IGCC	4665 Twist on wire connector
Type	Wire Connectors & Termination
Special Features	Three sizes accommodate #18-14AWG stranded Copper
Application	For high temperature applications over 105 degree C
Standard	UL E9809, CSA 6591
Conductor Range	#18- 14 AWG
Material	Porcelain
Color	White
Voltage Rating	300 V
Temperature Rating	Over 105 C ; Over 221 F

Packaging

Outer Quantity	100
Outer Dimensions (inches)	5.3x3x2.1
Weight Uom	3.75 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website