



Catalog Number: 1351
Product ID: 7TAD013550R0013
UPC Number: 78621001351
EAN Number: 05415022257403
Status: A



Actual



Representative

Pipe Spacer, Electro-galvanized Malleable Iron, Use with Conduit Sizes of 1-1/4 Inch, 1-1/2 Inch, and 2 Inch for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	31161816 Spacers or standoffs
IGCC	2894 Spacers or standoffs
Type	Rigid/IMC Conduit Fittings
Application	Provides Mounting Surface for Conduit Where Installation Requires Air Space Between Conduit and Supporting Surface
Standard	CSA
Material	Malleable Iron

European Specifications (ETIM)

ETIM	EC001494 Spacer for cable protection tube
Model	One fold
Suitable for pipe diameter	31.75-50.80mm

Packaging

Inner Quantity	25
Inner Dimensions (inches)	5xx1.66
Outer Quantity	50
Outer Dimensions (inches)	0x900x0
Weight Uom	28 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------