



Actual



Representative

Catalog Number: 140
Product ID: 7TAD012050R0001
UPC Number: 78621000140
EAN Number: 05414363101536
Status: A

3/8 Inch Steel Locknut for Use With Rigid/IMC Conduit

- Tightens without deformation
- To effectively bond conduit or connector to box or enclosure.

North American Specifications (UNSPSC)

UNSPSC	31161716 Locknuts
IGCC	2849 Locknuts
Type	Locknuts
Special Features	Hardened Steel, Malleable Iron, Copper-Free Aluminum Construction
Application	To Connect Externally Threaded Conduit or Connector to a Threadless Opening In a Box or Enclosure.
Standard	UL E23018, CSA
Material of Construction	Steel
Thread Size	3/8 in

European Specifications (ETIM)

ETIM	EC002382 Locknut
Material	Steel
Surface protection	Untreated
Height	23.88mm
With nylon ring	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	4.3x4x3.2
Outer Quantity	500
Outer Dimensions (inches)	16.4x4.7x5
Weight Uom	1.2 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------