



Actual



Representative

**Location:** KENT

**hozack**

19030-A 68TH AVE S

**Catalog Number:** 1451  
**Product ID:** 7TAD013460R0000  
**UPC Number:** 78621001451  
**EAN Number:** 05414363137733  
**Status:** A

1/2 Inch Non Metallic Knockout Plug, Thermoplastic for Use with Rigid/IMC Conduit

#### North American Specifications (UNSPSC)

UNSPSC	39121403 Locking plug
IGCC	4527 Locking plug
Type	Non-Metallic Locking Plug for Rigid/IMC Conduit
Special Features	One-Piece Construction Designed to Snap in Place
Application	To Plug Unused Knockout Openings In a Box or Enclosure
Standard	UL E13938, CSA
Material	Thermoplastic
Size	1/2 Inch

#### European Specifications (ETIM)

ETIM	EC002326 Cable plug for cable-/installation tube entry
Suitable for junction box	Y
For tubediameter	Other
Number of conduit lead-ins	1

#### Packaging

Inner Quantity	100
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	1000
Outer Dimensions (inches)	16.7x10.7x6.2
Weight Uom	10 lbs. per 1000

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

#### Header

3D Model	Available on Website
----------	----------------------