



Representative

Catalog Number: 1452
Product ID: 7TAD013460R0001
UPC Number: 78621001452
EAN Number: 05415022257281
Status: Active

3/4 Inch Non Metallic Knockout Plug, Thermoplastic for Use with Rigid/IMC Conduit

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121403 Locking plug
IGCC	4527 Locking plug
Brand Name	T&B
Type	Non-Metallic Locking Plug for Rigid/IMC Conduit
Special Features	One-Piece Construction Designed to Snap in Place
Application	To Plug Unused Knockout Openings In a Box or Enclosure
Standard	UL E13938, CSA
Material	Thermoplastic
Size	3/4 Inch

European Specifications (ETIM)

ETIM	EC002326 Cable plug for cable-/installation tube entry
Suitable for junction box	Y
For tubediameter	Other
Number of conduit lead-ins	1

Packaging

Inner Quantity	100
Inner Dimensions (inches)	1.25xx.68
Outer Quantity	1000
Outer Dimensions (inches)	0x900x0
Weight Uom	5.63 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com