



Representative

Catalog Number: 1454
Product ID: 7TAD013460R0003
UPC Number: 78621001454
EAN Number: 05415022258608
Status: A

1-1/4 Inch Non Metallic Knockout Plug, Thermoplastic for Use with Rigid/IMC Conduit

North American Specifications (UNSPSC)

UNSPSC	39121403 Locking plug
IGCC	4527 Locking plug
Type	Non-Metallic Locking Plug for Rigid/IMC Conduit
Special Features	One-Piece Construction Designed to Snap in Place
Application	To Plug Unused Knockout Openings In a Box or Enclosure
Standard	UL E13938, CSA
Material	Thermoplastic
Size	1-1/4 Inch

European Specifications (ETIM)

ETIM	EC002326 Cable plug for cable-/installation tube entry
Suitable for junction box	Y
For tubediameter	1 1/4 inch
Number of conduit lead-ins	1

Packaging

Inner Quantity	50
Inner Dimensions (inches)	6x5x4
Outer Quantity	100
Outer Dimensions (inches)	8.6x6.8x6
Weight Uom	2 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------