



Actual



Representative

Catalog Number: 148
Product ID: 7TAD012050R0010
UPC Number: 78621000148
EAN Number: 05414363101567
Status: A

3 Inch Malleable Iron Locknut for Use With Rigid/IMC Conduit

- Tightens without deformation
- To effectively bond conduit or connector to box or enclosure.

North American Specifications (UNSPSC)

UNSPSC	31161716 Locknuts
IGCC	2849 Locknuts
Type	Locknuts
Special Features	Hardened Steel, Malleable Iron, Copper-Free Aluminum Construction
Application	To Connect Externally Threaded Conduit or Connector to a Threadless Opening In a Box or Enclosure.
Standard	UL E23018, CSA
Material of Construction	Malleable Iron
Thread Size	3 in

European Specifications (ETIM)

ETIM	EC002382 Locknut
Material	Other
Surface protection	Untreated
Height	106.43mm
With nylon ring	N

Packaging

Inner Quantity	5
Inner Dimensions (inches)	5.2x4.6x3.1
Outer Quantity	25
Outer Dimensions (inches)	16.3x5.2x5.8
Weight Uom	35 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------