



Actual



Representative

**Catalog Number:** 152  
**Product ID:** 7TAD012050R0013  
**UPC Number:** 78621000152  
**EAN Number:** 05414363190646  
**Status:** A

5 Inch Malleable Iron Locknut for Use With Rigid/IMC Conduit

- Tightens without deformation
- To effectively bond conduit or connector to box or enclosure.

**North American Specifications (UNSPSC)**

UNSPSC	31161716 Locknuts
IGCC	2849 Locknuts
Type	Locknuts
Special Features	Hardened Steel, Malleable Iron, Copper-Free Aluminum Construction
Application	To Connect Externally Threaded Conduit or Connector to a Threadless Opening In a Box or Enclosure.
Standard	UL E23018, CSA
Material of Construction	Malleable Iron
Thread Size	5 in

**European Specifications (ETIM)**

ETIM	EC002382 Locknut
Material	Other
Surface protection	Untreated
Height	165.1mm
With nylon ring	N

**Packaging**

Inner Quantity	2
Inner Dimensions (inches)	8.1x4.8x7.1
Outer Quantity	4
Outer Dimensions (inches)	9.6x6.9x4.7
Weight Uom	120 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

**Header**

3D Model	Available on Website
----------	----------------------