



Representative

**Catalog Number:** 1942  
**Product ID:** 7TAD013120R0000  
**UPC Number:** 78621001942  
**EAN Number:** 05414363138655  
**Status:** A

1/2 Inch Chase Nipple, Steel, Nylon Insulated for Use with Rigid/IMC Conduit

#### North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Type	Chase Conduit Nipple
Application	To Effectively Bush Factory or Field-Punched, Cut, or Drilled Holes In Metal Boxes or Enclosures. To Couple Boxes Back-to-Back
Standard	UL E23018, CSA
Material	Steel
Trade Size	1/2 in

#### European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
Thread size outer thread metric	16
Material housing	Other
Material quality	Other
Surface protection	Untreated
Model	Straight

#### Packaging

Inner Quantity	25
Inner Dimensions (inches)	3x4x4
Outer Quantity	100
Outer Dimensions (inches)	8.8x7x5.1
Weight Uom	3.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-001846
--------------------------------	------------

#### Header

3D Model	Available on Website
----------	----------------------