



Actual



Representative

Catalog Number: 2278
Product ID: 7TBD105260R0029
UPC Number: 78621002278
EAN Number: 05414363190516
Status: A

Liquidtight Strain Relief Cord Connector, 1-1/4 Inch, 90 Degree Bend, Meets Coast Guard CG293, Cord Range 1.065 to 1.205 Inch, Malleable Iron

- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-90 Degree
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	1-1/4 Inch
Conductor Range	1.065 to 1.205 Inch
Material	Malleable Iron
Color	Metallic

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 1/4 inch
Thread length	17.462mm
Suitable for cable diameter	27.05-30.60mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	90°-elbow
Strain relief	Y

Packaging

Inner Quantity	2
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	10
Outer Dimensions (inches)	24.1x4x5.8
Weight Uom	94 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000047
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------