



Catalog Number: 2286
Product ID: 7TBD105250R0014
UPC Number: 78621002286
EAN Number: 05414363139195
Status: A



Actual



Representative

Liquidtight Strain Relief Cord Connector, 2 Inch, 90 Degree Bend, Meets Coast Guard CG293, Cord Range 1.625 to 1.875 Inch, Malleable Iron

- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-90 Degree
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	2 Inch
Conductor Range	1.625 to 1.875 Inch
Material	Malleable Iron
Color	Metallic

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	2 inch
Thread length	21.43mm
Suitable for cable diameter	41.275-47.625mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	90°-elbow
Strain relief	Y

Packaging

Inner Quantity	1
Inner Dimensions (inches)	5.6x3.3x4.6
Outer Quantity	5
Outer Dimensions (inches)	24x5.25x3.5
Weight Uom	1.8 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000047
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------