



Actual



Representative

Catalog Number: 2446
Product ID: 7TBD105140R0014
UPC Number: 78621002446
Status: A

Watertight Connector for Oval Cable, Hub Size 1 1/4 Inch, Die Cast Zinc Body with Neoprene Bushing, Oval Cable Range Maximum .750 X 1.150 Inch, Minimum .565 X .965 Inch

- The tapered neoprene bushings are resistant to oil, sunlight and water. Hex gland and body take the same wrench opening and a stainless steel slip ring prevents cable from twisting as gland ring is being tightened. Threads on the body are tapered for water

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Watertight Connectors for Oval Cable
Special Features	A Design with Two Tapers Inside The Body-A Slow One and a Fast One-Permits The Stocking of Fewer Connectors for Varied Cable Sizes and Allows Maximum Take-Up.
Application	To Connect Underground Feeder Cables to a Box or an Enclosure
Standard	UL E15170, CSA 4484
Size	1-1/4 Inch
Conductor Range	0.565x0.965 to 0.750x1.150 Inch
Material	Zinc Die Cast
Color	Metallic

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 1/4 inch
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Straight

Packaging

Inner Quantity	5
Inner Dimensions (inches)	6.3x3.3x4.69
Outer Quantity	50
Outer Dimensions (inches)	4x24.2x13.1
Weight Uom	55.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------