



Representative

Catalog Number: 2492
Product ID: 7TAA106030R0000
UPC Number: 78621002492
Status: A

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 3/8 Inch, Knockout Size 1/2 Inch, Cable Range 0.370 to 0.500 Inch, Steel with Zinc Plating, Nylon Insulated

- Removable bushing design covers wide range, reduces inventories.
- One screw provides quick installation
- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.
- Can be used on smooth or corrugated aluminum sheathed and steel metal clad cable.

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Unique Saddle Design Firmly Secures Cable In Place, Provides Holding Power In Excess of Listing Agency Requirements and Assures High Quality Bonding
Application	For Use with Armored Cable and Flexible Metal Conduit.
Standard	UL E23018, CSA 2884
Size	3/8 Inch
Conductor Range	0.370 to 0.500 Inch
Material	Steel
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel
Surface protection	Zinc coated

Packaging

Inner Quantity	100
Inner Dimensions (inches)	8.1x4.5x5.4
Outer Quantity	500
Outer Dimensions (inches)	8.1x5.4x4.1
Weight Uom	7.13 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------

