



Actual



Representative

Catalog Number: 2516
Product ID: 7TBD105260R0035
UPC Number: 78621002516
EAN Number: 05414363139287
Status: A

Liquidtight Strain Relief Cord Connector, 1/4 Inch, Straight, Cord Range 0.060 to 0.125 Inch, Steel

- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	CSA
Size	1/4 Inch
Conductor Range	0.060 to 0.125 Inch
Material	Steel
Color	Metallic
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/4 inch
Thread length	11.90mm
Suitable for cable diameter	1.52-3.75mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight
Strain relief	Y
Operating temperature	0-+105°C

Packaging

Inner Quantity	25
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	100
Outer Dimensions (inches)	7.8x7x4.2
Weight Uom	5.56 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000046
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------

