



Actual



Representative

Catalog Number: 2519
Product ID: 7TBD105250R0017
UPC Number: 78621002519
EAN Number: 05414363139294
Status: A

Liquidtight Strain Relief Cord Connector, 3/8 Inch, Straight, Cord Range 0.150 to 0.300 Inch, Steel

- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	3/8 Inch
Conductor Range	0.150 to 0.300 Inch
Material	Steel
Color	Metallic
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/8 inch
Thread length	11.90mm
Suitable for cable diameter	3.81-7.62mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight
Strain relief	Y
Operating temperature	0-+105°C

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x4x3
Outer Quantity	100
Outer Dimensions (inches)	9.1x8.8x4.1
Weight Uom	10.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000046
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------

