



Actual



Representative

Catalog Number: 2520-2
Product ID: 7TBD105010R0000
UPC Number: 78621058293
EAN Number: 05415022258141
Status: A

Multi-Hole Cord Connector with 2 Holes, Hub Size 1/2 Inch, Cord Diameter 0.210 to .230 Inch, Steel

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Multi-Hole Cord Connectors
Application	Ideal for Environments Where there is a Need to Run Multiple Cables Into an Enclosure and Space At The Enclosure is Limited.
Size	1/2 Inch
Conductor Range	0.210 to 0.230 Inch
Material	Steel
Color	Metallic
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.875mm
Suitable for cable diameter	5.33-5.84mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight

Packaging

Inner Quantity	25
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	100
Outer Dimensions (inches)	10.9x10.1x3.9
Weight Uom	15.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000082
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------