



Actual



Representative

Catalog Number: 2530-2
Product ID: 7TBD105020R0000
UPC Number: 78621058292
EAN Number: 05415022258912
Status: A

Multi-Hole Cord Connector with 2 Holes, Hub Size 3/4 Inch, Cord Diameter 0.210 to .230 Inch, Steel

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Multi-Hole Cord Connectors
Application	Ideal for Environments Where there is a Need to Run Multiple Cables Into an Enclosure and Space At the Enclosure is Limited.
Size	3/4 Inch
Conductor Range	0.210 to 0.230 Inch
Material	Steel
Color	Metallic
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	15.875mm
Suitable for cable diameter	5.33-5.84mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight

Packaging

Inner Quantity	10
Outer Quantity	100
Outer Dimensions (inches)	21.75x9x4
Weight Uom	21.19 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000082
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------