



Actual



Representative

**Catalog Number:** 2541-2  
**Product ID:** 7TBD105020R0002  
**UPC Number:** 78621058289  
**EAN Number:** 05415022512588  
**Status:** A

Multi-Hole Cord Connector with 2 Holes, Hub Size 1 Inch, Cord Diameter 0.290 to 0.310 Inch, Steel

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Multi-Hole Cord Connectors
Application	Ideal for Environments Where there is a Need to Run Multiple Cables Into an Enclosure and Space At the Enclosure is Limited.
Standard	UL E13938
Size	1 Inch
Conductor Range	0.290 to 0.310 Inch
Material	Steel
Color	Metallic
Temperature Rating	105 C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	19.83mm
Suitable for cable diameter	7.36-7.87mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight

### Packaging

Inner Quantity	10
Outer Quantity	30
Outer Dimensions (inches)	10.9x6.55x5.34
Weight Uom	30 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000082
Catalog Page	Available on Website
Support/Tools	Available on Website

### Header

3D Model	Available on Website
----------	----------------------