



Actual



Representative

**Catalog Number:** 2542-2  
**Product ID:** 7TBD105020R0005  
**UPC Number:** 78621058288  
**EAN Number:** 05415022512557  
**Status:** A

Multi-Hole Cord Connector with 2 Holes, Hub Size 1 Inch, Cord Diameter 0.365 to 0.385 Inch, Steel

**North American Specifications (UNSPSC)**

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Multi-Hole Cord Connectors
Application	Ideal for Environments Where there is a Need to Run Multiple Cables Into an Enclosure and Space At the Enclosure is Limited.
Standard	UL E13938
Size	1 Inch
Conductor Range	0.365 to 0.385 Inch
Material	Steel
Color	Metallic
Temperature Rating	105 C

**European Specifications (ETIM)**

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	19.83mm
Suitable for cable diameter	9.27-9.78mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight

**Packaging**

Inner Quantity	10
Outer Quantity	100
Outer Dimensions (inches)	24.5x13x4
Weight Uom	33 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000082
Support/Tools	Available on Website

**Header**

3D Model	Available on Website
----------	----------------------