



Actual



Actual

**Catalog Number:** 255-I  
**Product ID:** 7TAA106070R0006  
**UPC Number:** 78620989534  
**EAN Number:** 05414363449379  
**Status:** A

Squeeze Connector, Straight, Trade Size 3/4 Inch, Knockout Size 3/4 Inch, Cable Range 0.938 to 1.094 Inch, Insulated Throat, Steel

### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	T&B Squeeze Connectors Will Fit Every Size of Armored Cable, Leaded Cable and Flexible Conduit
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	3/4 Inch
Conductor Range	0.938 to 1.094 Inch
Material	Steel
Finish	Zinc Plated
Color	Metallic
Insulation	Insulated Throat

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel
Thread length	11.11mm

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	8.25x5.25x4.25
Outer Quantity	100
Outer Dimensions (inches)	10.5x8.75x8.75
Weight Uom	13 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000408
--------------------------------	------------