



Actual



Actual

Catalog Number: 256
Product ID: 7TAA106060R0001
UPC Number: 78621000256
EAN Number: 05414363139546
Status: A

Squeeze Connector, Straight, Trade Size 1 Inch, Knockout Size 1 Inch, Cable Range 1.250 to 1.375 Inch, Malleable Iron

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	T&B Squeeze Connectors Will Fit Every Size of Armored Cable, Leaded Cable and Flexible Conduit
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	1 Inch
Conductor Range	1.250 to 1.375 Inch
Material	Malleable Iron
Finish	Zinc Plated
Color	Metallic
Insulation	No

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Thread length	12.7mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Inner Quantity	5
Inner Dimensions (inches)	4x4x3
Outer Quantity	25
Outer Dimensions (inches)	16.75x4.5x4.75
Weight Uom	25 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------