



Actual



Representative

**Catalog Number:** 2577  
**Product ID:** 7TBD105250R0031  
**UPC Number:** 78621002577  
**EAN Number:** 05414363139966  
**Status:** A

Liquidtight Strain Relief Cord Connector, 2 Inch, Straight, Cord Range 1.937 to 2.187 Inch, Malleable Iron

- Meets Coast Guard CG293

**North American Specifications (UNSPSC)**

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	2 Inch
Conductor Range	1.937 to 2.187 Inch
Material	Malleable Iron
Color	Metallic
Temperature Rating	105 C

**European Specifications (ETIM)**

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	2 inch
Thread length	21.43mm
Suitable for cable diameter	49.20-55.55mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Straight
Strain relief	Y
Operating temperature	0-+105°C

**Packaging**

Outer Quantity	5
Outer Dimensions (inches)	9.8x7.9x4.3
Weight Uom	1.64 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000046
Support/Tools	Available on Website

**Header**

3D Model	Available on Website
----------	----------------------