



Actual



Representative

Catalog Number: 2585
Product ID: 7TBD105240R0025
UPC Number: 78621002585
EAN Number: 05414363139980
Status: A

Liquidtight Strain Relief Cord Connector, 2-1/2 Inch, Straight, Cord Range 1.937 to 2.187 Inch, Malleable Iron

- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	2-1/2 Inch
Conductor Range	1.937 to 2.187 Inch
Material	Malleable Iron
Color	Metallic
Temperature Rating	105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	2 1/2 inch
Thread length	26.19mm
Suitable for cable diameter	49.20-55.55mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Straight
Strain relief	Y
Operating temperature	0-+105°C

Packaging

Outer Quantity	5
Outer Dimensions (inches)	9.9x8.1x4.6
Weight Uom	212 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000046
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------