



Actual



Actual

**Catalog Number:** 258  
**Product ID:** 7TAA106070R0009  
**UPC Number:** 78621000258  
**Status:** A

Squeeze Connector, Straight, Trade Size 1-1/2 Inch, Knockout Size 1-1/2 Inch, Cable Range 1.688 to 1.875 Inch, Malleable Iron

### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	T&B Squeeze Connectors Will Fit Every Size of Armored Cable, Leaded Cable and Flexible Conduit
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	1-1/2 Inch
Conductor Range	1.688 to 1.875 Inch
Material	Malleable Iron
Finish	Zinc Plated
Color	Metallic
Insulation	No

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Thread length	14.29mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	8x5x4
Outer Quantity	10
Outer Dimensions (inches)	8.8x5.6x8.8
Weight Uom	83.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website