



Actual



Representative

**Catalog Number:** 2593  
**Product ID:** 7TBD105250R0034  
**UPC Number:** 78621002593  
**EAN Number:** 05414363140023  
**Status:** A

Liquidtight Strain Relief Cord Connector, 3 Inch, Straight, Cord Range 2.350 to 2.565 Inch, Malleable Iron

- Meets Coast Guard CG293

**North American Specifications (UNSPSC)**

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	3 Inch
Conductor Range	2.350 to 2.565 Inch
Material	Malleable Iron
Color	Metallic
Temperature Rating	105 C

**European Specifications (ETIM)**

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3 inch
Thread length	26.19mm
Suitable for cable diameter	59.69-65.151mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Straight
Strain relief	Y
Operating temperature	0-+105°C

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	6.1x4.7x5.9
Weight Uom	3.8 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet	TDS000046
Support/Tools	Available on Website

**Header**

3D Model	Available on Website
----------	----------------------