



Actual



Representative

Catalog Number: 2639
Product ID: 7TAD105150R0003
UPC Number: 78621002639
EAN Number: 05414363190561
Status: A

Chase Liquidtight Steel Cord Connector, Straight, 3/4 Inch, Cord Range 0.375 to 0.500 Inch

- Suitable for use in hazardous locations in Class I, Div. 2; Class II, Div 1 & 2; Class III, Div 1 & 2, where general purpose equipment is specifically permitted by NEC 500-2(a)
- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Flexible Cord and Cable Fittings
Special Features	CSA Certified Watertight. UL Listed As Liquidtight Strain Relief, and Outlet Bushing.
Application	For Installation Where Space is Limited Inside the Enclosure
Standard	CSA, UL E13938
Size	3/4 Inch
Material	Steel

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Suitable for cable diameter	9.525-12.7mm
Material	Other
Material quality	Steel
Colour	Natural colour
Model	Straight

Packaging

Inner Quantity	25
Inner Dimensions (inches)	8.5x4.19x5.8
Outer Quantity	50
Outer Dimensions (inches)	10.8x8.39x4.5
Weight Uom	30 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000049
Catalog Page	Available on Website
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------