



Actual



Representative

**Catalog Number:** 2640  
**Product ID:** 7TAD105150R0004  
**UPC Number:** 78621002640  
**EAN Number:** 05414363140108  
**Status:** A

Chase Liquidtight Steel Cord Connector, Straight, 3/4 Inch, Cord Range 0.500 to 0.625 Inch

- Meets Coast Guard CG293

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	Chase Cord Connectors-Straight
Application	Suitable for use in hazardous locations in Class I, Div. 2; Class II, Div 1 & 2; Class III, Div 1 & 2, where general purpose equipment is specifically permitted by NEC 500-2(a).
Standard	UL E13938, CSA
Size	3/4 Inch
Material	Steel
Temperature Rating	105 C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Suitable for cable diameter	12.7-15.875mm
Material	Other
Material quality	Steel
Colour	Natural colour
Model	Straight

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	50
Outer Dimensions (inches)	8.4x5.3x8.5
Weight Uom	31 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000049
Catalog Page	Available on Website
Support/Tools	Available on Website

### Header

3D Model	Available on Website
----------	----------------------