



Actual



Representative

Catalog Number: 2646
Product ID: 7TAD105150R0005
UPC Number: 78621084327
EAN Number: 05414363190653
Status: A

Chase Liquidtight Cord Connector, 1 Inch, Straight, Steel Body and Gland, Neoprene Bushing, Cord Range 0.500 to 0.625 Inch, Throat Diameter 1 Inch, Metallic

North American Specifications (UNSPSC)

| | |
|--------------------|---|
| UNSPSC | 39121431 Cable gland connector |
| IGCC | 4601 Cable gland connector |
| Type | Chase Cord Connectors-Straight |
| Application | Suitable for Use In Hazardous Locations In Class I, Div. 2; Class II, Div 1 & 2; Class III, Div 1 & 2, Where General Purpose Equipment is Specifically Permitted by NEC 500-2(A). |
| Standard | UL E13938, CSA 589 |
| Size | 1 Inch |
| Conductor Range | 0.500 to 0.625 Inch |
| Material | Steel |
| Color | Metallic |
| Temperature Rating | 105 C |

European Specifications (ETIM)

| | |
|--|----------------------------|
| ETIM | EC000441 Cable screw gland |
| Thread type | NPT |
| Nominal thread size inch/gas pipe thread | 1 inch |
| Suitable for cable diameter | 12.7-15.875mm |
| Material | Other |
| Material quality | Steel |
| Colour | Natural colour |
| Model | Straight |

Packaging

| | |
|---------------------------|-----------------|
| Inner Quantity | 5 |
| Inner Dimensions (inches) | 4.12x4.12x3.12 |
| Outer Quantity | 25 |
| Outer Dimensions (inches) | 16.5x4.5x4.5 |
| Weight Uom | 50 lbs. per 100 |

Documents / Support Tools

| | |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet | TDS000049 |
| Technical Drawing / Data Sheet US | Available on Website |
| Support/Tools | Available on Website |

Header

| | |
|----------|----------------------|
| 3D Model | Available on Website |
|----------|----------------------|