



Actual



Representative

**Catalog Number:** 2680  
**Product ID:** 7TAD105050R0004  
**UPC Number:** 78621002680  
**EAN Number:** 05415022512618  
**Status:** A

Liquidtight Cord Connector, 3/8 Inch, 90 Degree Bend, Cord Range 0.125 to 0.275 Inch, Meets Coast Guard CG293, Nylon, Black

- Segmented chuck provides high mechanical pullout performance, will not cut or damage cord jacket.
- Temperature Rating: -34 to +105 Degrees Celsius
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC. Class I, Div 2; Class II, Div 1 & 2; Class III, Div 1 & 2; NEC 501-4(b), 502-4(a)(b), 503-3(a)(b)
- Meets Coast Guard CG293

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-90 Degree
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	To Connect Flexible Cord to a Box or Enclosure and Provide Adequate Strain Relief.
Standard	UL E13938, CSA
Size	3/8 Inch
Conductor Range	0.125 to 0.275 Inch
Material	Nylon
Color	Black
Temperature Rating	-34 to +105 C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/8 inch
Thread length	11.68mm
Suitable for cable diameter	3.175-6.985mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Black
Model	90°-elbow
Operating temperature	-34-+105°C

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	100
Outer Dimensions (inches)	9.8x8x7
Weight Uom	3 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000053
Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA01320-TB2
Support/Tools	Available on Website

### Header

3D Model

Available on Website