



Actual



Representative

Catalog Number: 2696
Product ID: 7TAD105040R0012
UPC Number: 78621002696
EAN Number: 05415022495751
Status: A

Liquidtight Cord Connector, 3/4 Inch, Straight, Cord Range 0.770 to 0.895 Inch, Meets Coast Guard CG293, Nylon, Black

- Segmented chuck provides high mechanical pullout performance, will not cut or damage cord jacket.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC. Class I, Div 2; Class II, Div 1 & 2; Class III, Div 1 & 2; NEC 501-4(b), 502-4(a)(b), 503-3(a)(b)
- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-Straight
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	To Connect Flexible Cord to a Box or Enclosure and Provide Adequate Strain Relief.
Standard	UL E13938, CSA
Size	3/4 Inch
Conductor Range	0.770 to 0.895 Inch
Material	Nylon
Color	Black
Temperature Rating	-34 to +105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	15.875mm
Suitable for cable diameter	19.558-22.733mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Black
Model	Straight
Operating temperature	-34-+105°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x4x4
Outer Quantity	100
Outer Dimensions (inches)	16.6x12.8x9.9
Weight Uom	13 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000052
Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Instruction Sheet	TA01320-TB2
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------

