



**Catalog Number:** 269  
**Product ID:** 7TAA106060R0006  
**UPC Number:** 78621000269  
**Status:** A



Actual

Squeeze Connector, 45 Degree Bend, Trade Size 3/4 Inch, Knockout Size 3/4 Inch, Cable Range 1.000 to 1.125 Inch, Steel

#### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Fast and Easy Installation, Simply Loosen Screws Partway to Lift off Cap
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA 2884
Size	3/4 Inch
Conductor Range	1.000 to 1.125 Inch
Material	Malleable Iron
Finish	Zinc Plated
Color	Metallic
Insulation	No

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel
Thread length	39.68mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

#### Packaging

Inner Quantity	25
Inner Dimensions (inches)	10.4x7.2x4.5
Outer Quantity	50
Outer Dimensions (inches)	12.3x11.8x9.3
Weight Uom	25 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------