



Representative

Catalog Number: 2706
Product ID: 7TAD105040R0017
UPC Number: 78621002706
EAN Number: 05415022495775
Status: A

Liquidtight Cord Connector, 1-1/2 Inch, Straight, Cord Range 1.140 to 1.400 Inch, Meets Coast Guard CG293, Nylon, Black

- Segmented chuck provides high mechanical pullout performance, will not cut or damage cord jacket.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC. Class I, Div 2; Class II, Div 1 & 2; Class III, Div 1 & 2; NEC 501-4(b), 502-4(a)(b), 503-3(a)(b)
- Meets Coast Guard CG293

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-Straight
Special Features	Hand Tightens, No Tools Needed for Assembly
Application	To Connect Flexible Cord to a Box or Enclosure and Provide Adequate Strain Relief.
Standard	UL E13938, CSA
Size	1-1/2 Inch
Conductor Range	1.140 to 1.400 Inch
Material	Nylon
Color	Black
Temperature Rating	-34 to +105 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 1/2 inch
Thread length	20.64mm
Suitable for cable diameter	28.956-35.56mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Black
Model	Straight
Operating temperature	-34-+105°C

Packaging

Inner Quantity	2
Inner Dimensions (inches)	6x5x4
Outer Quantity	10
Outer Dimensions (inches)	13.25x11x6
Weight Uom	50 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000052
Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA01320-TB2
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------

