



Representative

Catalog Number: 2827
Product ID: 7TAD105130R0003
UPC Number: 78621002827
Status: A

UF Cable Fitting, 1/2 Inch, Cable Range Maximum .550 x .280, Minimum .400 x .190 Inch, Nylon, Black

- Tapered threaded hub, liquidtight and dust tight; hand tightens-no tools required. Corrosive and weather resistant nylon for outdoor and indoor applications.

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	UF Cable Fittings
Special Features	Tapered Threaded Hub, Liquidtight and Dust Tight; Hand Tightens-No Tools Required. Corrosive and Weather Resistant Nylon.
Application	Indoor and Outdoor Use
Standard	UL E17583, CSA, RoHS
Size	1/2 Inch
Conductor Range	0.400x0.190 to 0.550 to 0.280 Inch
Material	Nylon
Color	Black

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.24mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Black
Model	Straight

Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x5x4
Outer Quantity	100
Outer Dimensions (inches)	12.8x8.7x6
Weight Uom	6 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA02460-TB2

Header

3D Model	Available on Website
----------	----------------------