



Actual

**Catalog Number:** 2922S  
**Product ID:** 7TBD105190R0002  
**UPC Number:** 78621029739  
**Status:** A

Liquidtight Strain Relief Connector, 1/2 Inch, Straight, Cord Range 0.500 to 0.750 Inch, Throat Diameter 9/16 Inch, Steel Body and Gland, Plastic Grip, Santoprene Bushing

#### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-Straight
Special Features	Extended Range with Superior Strain Relief
Application	A Liquidtight Fitting to Secure Flexible Cord or Power Cable to a Box or Enclosure and Provide Strain Relief.
Standard	CSA
Size	1/2 Inch
Conductor Range	0.500 to 0.750 Inch
Material	Steel
Color	Metallic

#### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.875mm
Suitable for cable diameter	12.7-19.05mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight
Strain relief	Y

#### Packaging

Inner Quantity	25
Outer Quantity	100
Outer Dimensions (inches)	13x11x5
Weight Uom	24.5 lbs. per 100

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------