



Actual

Catalog Number: 2930S
Product ID: 7TBD105190R0003
UPC Number: 78621029742
Status: A

Liquidtight Strain Relief Connector, 3/4 Inch, Straight, Cord Range 0.125 to 0.375 Inch, Throat Diameter 13/16 Inch, Steel Body and Gland, Plastic Grip, Santoprene Bushing

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-Straight
Special Features	Extended Range with Superior Strain Relief
Application	A Liquidtight Fitting to Secure Flexible Cord or Power Cable to a Box or Enclosure and Provide Strain Relief.
Standard	CSA
Size	3/4 Inch
Conductor Range	0.125 to 0.375 Inch
Material	Steel
Color	Metallic

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	19.05mm
Suitable for cable diameter	3.175-9.525mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight
Strain relief	Y

Packaging

Inner Quantity	10
Outer Quantity	100
Weight Uom	27.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------