



Actual

Catalog Number: 2931S
Product ID: 7TBD105190R0004
UPC Number: 78621029743
EAN Number: 05415022259094
Status: A

Liquidtight Strain Relief Connector, 3/4 Inch, Straight, Cord Range 0.310 to 0.560 Inch, Throat Diameter 13/16 Inch, Steel Body and Gland, Plastic Grip, Santoprene Bushing

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B Industrial Fitting
Type	Flexible Cord and Cable Fittings
Application	A Liquidtight Fitting to Secure Flexible Cord or Power Cable to a Box or Enclosure and Provide Strain Relief.
Standard	CSA
Size	3/4 Inch
Conductor Range	0.310 to 0.560 Inch
Material	Steel
Color	Metallic

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	19.05mm
Suitable for cable diameter	7.874-14.224mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight
Strain relief	Y

Packaging

Inner Quantity	10
Outer Quantity	100
Weight Uom	21.88 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------