



Actual

**Catalog Number:** 2940S  
**Product ID:** 7TBD105190R0007  
**UPC Number:** 78621029745  
**Status:** Active

Liquidtight Strain Relief Connector, 1 Inch, Straight, Cord Range 0.310 to 0.560 Inch, Throat Diameter 1-1/16 Inch, Steel Body and Gland, Plastic Grip, Santoprene Bushing

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B Industrial Fitting
Type	Cord Connectors-Straight
Special Features	Extended Range with Superior Strain Relief
Application	A Liquidtight Fitting to Secure Flexible Cord or Power Cable to a Box or Enclosure and Provide Strain Relief.
Standard	CSA
Size	1 inch
Conductor Range	0.125 to 0.375 Inch
Material	Steel
Color	Metallic

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	20.64mm
Suitable for cable diameter	3.175-9.525mm
Material	Metal
Material quality	Steel
Colour	Natural colour
Model	Straight
Strain relief	Y

### Packaging

Inner Quantity	10
Outer Quantity	100
Weight Uom	42.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website