



Actual



Representative

Catalog Number: 2941NM
Product ID: 7TAD105210R0003
UPC Number: 78621079747
EAN Number: 05414363101857
Status: A

Liquidtight Strain Relief Connector, Straight, 1 Inch NPT Thread, Cable Range 0.500 Inch/12.7mm to 0.750 Inch/19.0mm, IP65 Rating, UV Resistant Polyamide 6.6 Body, Black

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Cord Connectors-Straight
Special Features	Extended Range with Superior Strain Relief
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead
Standard	UL E13938, CSA 52391
Size	1 Inch
Conductor Range	0.500 Inch/12.7mm to 0.750 Inch/19.0mm
Material	Polyamide/Nylon 6.6
Color	Black
Temperature Rating	-34 to +105 C
Environmental Conditions	Ordinary, Wet, or Dry Locations

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	19.84mm
Suitable for cable diameter	12.7-19.0mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP65
Colour	Black
Model	Straight
Strain relief	Y
Operating temperature	-34-+105°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	100
Outer Dimensions (inches)	21.7x9.3x6.3
Weight Uom	9.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000050
Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00927-TB2
Support/Tools	Available on Website



Header

3D Model

Available on Website