



Representative

**Catalog Number:** 308  
**Product ID:** 7TAA106030R0001  
**UPC Number:** 78621000308  
**Status:** A

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 1-1/4 Inch, Knockout Size 1-1/4 Inch, Cable Range 1.562 to 1.750 Inch, Malleable Iron with Zinc Plating

- For use with Armored Cable and Flexible Metal Conduit

### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Easy to Install with Double Grip Saddle, Connectors are Completely Salvageable
Application	To Connect and Effectively Bond Metal-Clad Cables, Armored Cable, and Flexible Metal Conduit to a Box or Enclosure
Standard	UL E23018, CSA
Size	1-1/4 Inch
Conductor Range	1.562 to 1.750 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	No

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated
Thread length	39.68mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	4x4.5x6
Outer Quantity	10
Outer Dimensions (inches)	9.2x5.4x7.3
Weight Uom	59 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

### Header

3D Model	Available on Website
----------	----------------------

