



Representative

Catalog Number: 3115
Product ID: 7TAA106020R0003
UPC Number: 78621003115
EAN Number: 05414363140801
Status: A

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 3/4 Inch, Knockout Size 3/4 Inch, Cable Range 0.906 to 1.125 Inch, Steel with Zinc Plating, Nylon Insulated

- The tough lining of insulation and the Tite-Bite principles make these connectors a must when conductors are subject to conditions of vibration or strain.
- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Unique Saddle Design Firmly Secures Cable In Place, Provides Holding Power In Excess of Listing Agency Requirements and Assures High Quality Bonding
Application	For Use with Armored Cable and Flexible Metal Conduit.
Standard	UL E23018, CSA 2884
Size	3/4 Inch
Conductor Range	0.906 to 1.125 Inch
Material	Steel
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel
Surface protection	Zinc coated
Total length	32.54mm

Packaging

Inner Quantity	10
Inner Dimensions (inches)	4.5x5x3
Outer Quantity	50
Outer Dimensions (inches)	16.25x4.75x5.75
Weight Uom	17.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------

