

Catalog Number: 3118-60
Product ID: 7TAA106040R0010
UPC Number: 78621094794
Status: Active

1-1/4 Armored Cable/ Flexible Conduit Connector - Insulated, Cable Opening 1.562 Inch to 1.750 Inch, CSA Certified for TECK Armored Cable, UL Listed for 1-1/4 Inch FEFMC, FER-WFMC and ALRWFMC

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	T&B
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Unique Saddle Design Firmly Secures Cable In Place, Provides Holding Power In Excess of Listing Agency Requirements and Assures High Quality Bonding
Application	For Use with Armored Cable and Flexible Metal Conduit.
Standard	UL E23018, CSA 2884
Size	1-1/4 Inch
Connection	90 Degree
Conductor Range	1.562 to 1.750 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Untreated

Packaging

Outer Quantity	60
Outer Dimensions (inches)	12.87x10.75x8.62
Weight Uom	55 lbs. per 100