



Representative

**Catalog Number:** 3119-50  
**Product ID:** 7TAA106030R0005  
**UPC Number:** 78621094771  
**Status:** A

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 1-1/2 Inch, Knockout Size 1-1/2 Inch, Cable Range 1.812 to 2.031 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

#### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	The Tough Lining of Insulation and The Tite-Bite Principles Make These Connectors a Must When Conductors are Subject to Conditions of Vibration or Strain.
Application	For Use with Armored Cable and Flexible Metal Conduit.
Standard	UL E23018
Size	1-1/2 Inch
Conductor Range	1.812 to 2.031 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated

#### Packaging

Outer Quantity	50
Outer Dimensions (inches)	13x11x9
Weight Uom	1.03 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

#### Header

3D Model	Available on Website
----------	----------------------