



Representative

Catalog Number: 3120-30
Product ID: 7TAA106030R0008
UPC Number: 78621094770
Status: A

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 2 Inch, Knockout Size 2 Inch, Cable Range 2.312 to 2.500 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	The Tough Lining of Insulation and The Tite-Bite Principles Make These Connectors a Must When Conductors are Subject to Conditions of Vibration or Strain.
Application	For Use with Armored Cable and Flexible Metal Conduit.
Standard	UL E23018
Size	2 Inch
Conductor Range	2.312 to 2.500 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated

Packaging

Outer Quantity	30
Outer Dimensions (inches)	12.75x11x9
Weight Uom	155 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------