



Representative

Catalog Number: 312
Product ID: 7TAA106030R0006
UPC Number: 78621000312
Status: A

2 Inch. Tite-Bite Connector, Malleable Iron-Electro Zinc Plated, Insulator-Thermoplastic.

- For use with Armored Cable and Flexible Metal Conduit

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	Easy to Install with Double Grip Saddle, Connectors are Completely Salvageable
Application	To Connect and Effectively Bond Metal-Clad Cables, Armored Cable, and Flexible Metal Conduit to a Box or Enclosure
Standard	UL E23018, CSA
Size	2 Inch
Conductor Range	2.312 to 2.500 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	No

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated
Thread length	58.73mm
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y

Packaging

Outer Quantity	5
Outer Dimensions (inches)	9.6x6.8x3.8
Weight Uom	163.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website

Header

3D Model	Available on Website
----------	----------------------

