



Representative

Catalog Number: 3130-C
Product ID: 7TAA106040R0011
UPC Number: 78621036082
Status: A

3/8 Inch Armored Cable Tite-Bite Connector, 90 Degree Angle, For Aluminum and Steel FMC and AC Cable Opening .470 Inch to .590 Inch, Grounding Type, CSA Certified for Armored Cable Teck, UL Listed for Metal Clad Cables Type MC for Use in Dry Locations Only, For Interlocking or Corrugated Armor

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armoured Cable and Flexible Metal Conduit Fittings
Application	To Connect and Effectively Bond Armoured Cable or Flexible Metal Conduit to a Box or an Enclosure
Standard	UL
Size	3/8 Inch
Material	Steel
Finish	Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Thread length	3.97mm

Packaging

Inner Quantity	25
Outer Quantity	100
Weight Uom	10.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------