



Representative

Catalog Number: 3142
Product ID: 7TAA106030R0019
UPC Number: 78621003142
Status: A

Metal-Clad and Armored Cable Fitting, 90 Degree Bend, Trade Size 3 Inch, Knockout Size 3 Inch, Cable Range 3.312 to 3.562 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

- All the advantages of the straight connector with only one screw to tighten, except in the larger sizes where there are two.
- A peep hole on top provides for easy inspection of the ABC bushing.
- Narrow design makes it easy to install connectors in adjacent knockouts.
- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	By Far The Easiest and Best to Install When Making Sharp Bends At The Enclosure or Equipments
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA
Size	3 Inch
Conductor Range	3.312 to 3.562 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other
Surface protection	Zinc coated
Thread length	25.4mm

Packaging

Outer Quantity	1
Outer Dimensions (inches)	10.5x5.3x6.8
Weight Uom	737.5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------

